



ENGLISH

Datasheet

Stock No: 236-206

RS Pro Incandescent Beacon, Rotating, Surface Mount, 230 V ac



Product Details

Rotating Filament Beacons

Weatherproof and dustproof to IP56 these beacons offer high quality solutions for industrial environments and process applications.

High protection rating of IP56

Magnetic version is rated to 70mph

Optional cage guard for three-point mounting versions

Surge protection for safety against peak voltage

Full internal suppression for maximum interference reduction

166mm diameter footprint

125 rotations per minute

Note

Lens must be purchased separately

Supplied with

Appropriate SES (E14) 60W bulb (except the 12/24V versions, which are not supplied with a bulb)

Filament



ENGLISH

Specifications

Supply Voltage	230 V ac
Light Effect	Rotating
Lens Colour	Lens Not Included
Mounting Style	Surface Mount
Bulb Type	Incandescent
Current Type	AC
Base Diameter	166mm
Housing Colour	Black
Lamp Included	Yes
Series	V10993
Height	207mm
Maximum Temperature	+50°C
Minimum Temperature	-30°C