

## Terminals



### DKL 04

- Rated connecting capacity: 1,5-6 mm<sup>2</sup>, Cu

- for insertion in cable junction boxes
- 5-pole per pole 6 x 1.5 mm<sup>2</sup> sol, 4 x 2.5 mm<sup>2</sup> sol, 3 x 4 mm<sup>2</sup> sol, 2 x 6 mm<sup>2</sup> sol
- for cable junction boxes D 8020, D 8120, D 8040, D 9020, D 9120, D 9040, D 9220, DP 9020, DP 9220, DE 9320, DE 9321, DE 9340, DE 9341, KF 4020, KF 4040, KF 5020, KF 5040, KF 8020, KF 8040, KF 9020, KF 9040, KD 5020, KD 5040, KD 4020, KD 4040
- complete with fixing elements

rated insulation voltage	Ui = 690 V a.c./d.c.
Dismantling length	11 mm
tightening torque for terminal	1,2 Nm
Weight	0,025 kg

## Drawings

Dimension drawing

