



ENGLISH

Datasheet

DC Axial Fan, 120 x 120 x 25mm, 151.3m/h, 5W, 24V dc

RS Stock number [541-5362](#)



Specification:

Speed (RPM): 2200

Airflow (CFM): 89

Noise: (dB): 39

Volts DC: 24

Input Power (Watts) 5

Amps (max) 0.19

Max. Static Pressure ("H2O): 0.14

Frame & Impeller: PBT, UL94V-O plastic

Connection: 2x Lead wires 24AWG

Motor: Brushless DC, auto restart, polarity protected

Bearing System: Dual ball bearing

Insulation Resistance: 10M ohm between lead wire and frame (500VDC)

Dielectric Strength: 1 second at 500 VAC, max leakage - 500 Micro Amp

Temperature Range: -10C ~ +70C

Life (L10): 65,000 hours (45C)

Dimensions:

