




REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
03 ₂	SEE ECN 80-0084	G.B. 2/14/80	T.S. 2/19/80
03 ₃	REDRAWN IN CAD PER ECN 88-0678	E.F.H. 1/10/90	KCM

HOUSING	STAINLESS STEEL PER ASTM-A484 AND ASTM- A582, TYPE 303	GOLD PLATE PER MIL-G-45204 OVER NICKEL PLATE PER QQ-N-290
DIELECTRIC	TFE FLUOROCARBON PER ASTM-D-1457, MIL-P-19468, AND FED. SPEC L-P-403	N/A
CENTER CONTACT	BERYLLIUM COPPER PER ASTM B196, ALLOY 173	GOLD PLATE PER MIL-G-45204 OVER COPPER PLATE PER MIL-C-14550
COMPONENT	MATERIAL	FINISH

NOTES:

1. DESIGNED FOR USE WITH .085 DIA
SEMI-RIGID CABLE
2. CAPTURED CENTER CONTACT

CABLE ENTRY DIAMETER MINIMUM		UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES TOLERANCE ON		DRAWN BY R.M.K.		DATE 9/3/69		 AMP Incorporated 140 Fourth Avenue Waltham, MA 02451-7599			
HOUSING		FRAC. DEC. ANGLES		CHECKED BY B.D.		9/8/69					
CONTACT		± 1/64 ±.005 ± 1°		APPD BY G.B.		9/8/69					
	.089	These drawings and specifications are the property of Omni Spectra Incorporated and shall not be reproduced or copied or used in whole or in part as the basis for the manufacture or sale of item(s) without written permission.		USE ASS'Y PROCEDURE 408-04833 NO. AP. (20-010)		TITLE OSM STRAIGHT CABLE JACK DIRECT SOLDER ATTACHMENT					
	.021										
				SIZE B		CODE IDENT NO. 26805		2002-5016-00		REV 03 ₃	
				SCALE 5:1						SHEET 1 OF 1	

CUSTOMER DRAWING

AMP PART # 1050859-1
SHEET 1 OF 1 REV A