

## Insert label - PMST (9X38) OG - 0830966

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)


Insert label, orange, labeled, Mounting type: snapped into marker carrier, Lettering field: 9 x 38 mm



### Why buy this product

- The medium marking label is used in conjunction with insertable UCT-PMP ... labels in the CARRIER-PMP
- They are used to clearly identify devices and control cabinets
- They are secured in the CARRIER-PMP using rivets

### Key commercial data

Packing unit	100 pc
Minimum order quantity	100 pc
GTIN	 4 046356 912402
Weight per Piece (excluding packing)	0.47 g
Custom tariff number	39199000
Country of origin	Germany
Note	Made to Order (non-returnable)

### Technical data

#### Dimensions

Length (b)	38 mm
Width (a)	9 mm

#### Ambient conditions

Ambient temperature (operation)	-30 °C ... 80 °C
Recommended storage conditions	10-30 °C / 40-70 % relative humidity. Storage in the original packaging is recommended prior to processing.

#### General

Color	orange
Components	Silicone-free
Inflammability class according to UL 94	V0
Material	PVC
Wipe resistance	DIN EN 61010-1 (VDE 0411-1)

## Insert label - PMST (9X38) OG - 0830966

### Technical data

#### General

Number of individual labels	1
Number of individual labels per row	1
Marking mounting type	snapped into marker carrier

### Classifications

#### eCl@ss

eCl@ss 4.1	27141199
eCl@ss 5.1	27371301
eCl@ss 6.0	27371301

#### ETIM

ETIM 4.0	EC000761
ETIM 5.0	EC000761