

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

- - -

©

COPYRIGHT

-

BY TYCO ELECTRONICS CORPORATION.

ALL INTERNATIONAL RIGHTS RESERVED.

LOC

DIST

REVISIONS

AF

50

P

LTR

DESCRIPTION

DATE

DWN

APVD

C



REV PER ECR 10-021103

06DEC10



JR

PD


1 CONTINUOUS STRIP ON REELS.

NICKEL PLATE 0.00381 [.000150]
MIN THK.

SECTION A-A



SECTION B-B



SECTION C-C

2.29-3.30 DIA
[.090-.130] DIA

[#20-#16] AWG

0.813±0.025
[.032±.001]

63850-1

INSULATION RANGE

WIRE SIZE

MATING TAB
THICKNESS

PART NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN JR RUTH 9/19/95

CHK MS FEHER 9/19/95

APVD R REINER 9/19/95

PRODUCT SPEC

-

APPLICATION SPEC

-

WEIGHT -

CUSTOMER DRAWING



Tyco Electronics Corporation

Harrisburg, PA 17105-3608

NAME

RECEPTACLE, FASTON,
4.75 [.187] SERIES

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A3


00779

C-63850

SCALE 5:1

SHEET 1 OF 1

REV C

DIMENSIONS:
MM [INCHES]TOLERANCES UNLESS
OTHERWISE SPECIFIED:0 PLC ± -
1 PLC ± -
2 PLC ± 0.25 [.010]
3 PLC ± -
4 PLC ± -
ANGLES ± -

MATERIAL

T2 C.R.STEEL

FINISH

