

## CUSTOMER DATA SHEET

CDS No: **07302010**  
 Product: **WYPALL® L30 WIPERS – Centrefeed rolls/Blue**

Status: **Authorised**  
 Date: **27.08.03**  
 Replaces: **New**

Countries sold into: **All European Countries**

## BASESHEET

Property	Typical Values	Property	Typical Values
Recycled Fibre %	100%	Bleaching Method	ECF
Virgin Fibre %	0%	Ash Content	<2%
Broke – internal waste %	Up to 20%	Textured	Yes

## FINISHED PRODUCT

Property	Typical Values
Format	Folded/Roll Rolled
Basis Weight/No Plies	g/m <sup>2</sup> /No Plies 50/2
Thickness	mm/sheet N/M
Water Absorbency Capacity	% 600 to 1000
Water Absorbency Rate	sec Less than 3s
Oil Absorbency Capacity	% 350 to 550
Oil Absorbency Rate	sec 30 to 80
Machine Direction Tensile	N/m/ 2ply 511
Cross Direction Tensile	N/m/ 2ply 456
Wet Cross Direction Tensile	N/m/ 2ply 112
Colour – Technibrite	L* a* b* 68.15 -1.9 -17.74
Sheet Count	sheets 300
Sheet Length	mm 380
Sheet Width	mm 206
Roll Diameter	mm 200

## PALLETISATION

Unit of Sale: 6 items per case	Nett Weight/Case:	7.3Kg		
Case Size L x W x H: 60.0 x 40.0 x 20.6 cm	Max Weight/Case:	8.0Kg		
Type of Packaging: Poly/Shrinkwrap	Dispenser Codes:	7087/7088		
Pallet Type	Euro	0.5 Euro	GKN	0.5 GKN
No. Case/Roll per Pallet	32	24	45	30
No. Cases per Layer	4	4	5	5
No. Layers per Pallet	8	6	9	6

## ADDITIONAL INFORMATION

### Food Contact Tissue (Kitchen Towel, Napkins & Wipers)

Germany, Switzerland	BfR Recommendation XXXVI	Yes	<del>No</del>
EU	Council of Europe Guidelines	N/A	N/A
ISO 9001 : 2000		Yes	<del>No</del>

## NOTE

This data was generated from samples which were taken to be typical of standard product. The data is given for information only. Additional information can be supplied on request.

## CONFIDENTIALITY STATEMENT

These specifications and the confidential information contained herein are the property of Kimberly-Clark. Copies of this material are the property of Kimberly-Clark and should be made only if absolutely necessary. Copies, like the originals, are considered as trade secrets.