

Customer Information Sheet

DRAWING No.: M50-311XX42

SHEET 2 OF 2




IF IN DOUBT - ASK

(C)

NOT TO SCALE

THIRD ANGLE PROJECTION

ALL DIMENSIONS IN mm



RECOMMENDED PCB LAYOUT

SPECIFICATIONS:

MATERIAL:

MOULDING - HIGH TEMP THERMOPLASTIC UL94V-0
CONTACTS - HIGH STRENGTH COPPER ALLOY

FINISH:

CONTACT - 0.02-0.08μ GOLD ON CONTACT AREA,
2.5-3.8μ 100% TIN ON TAILS

ELECTRICAL:

CURRENT RATING - (ALL CONTACTS ARE
ELECTRICALLY LOADED) - 1 AMP
CONTACT RESISTANCE - 30 MILLIOHMS MAX
INSULATION RESISTANCE - 1000 MEGOHMS MIN
DIELECTRIC WITHSTANDING - 250V AC MIN

MECHANICAL:

CONTACT RETENTION - 3.0N NOMINAL
INSERTION FORCE - 0.56N NOMINAL
WITHDRAWAL FORCE - 0.15N MIN
SOLDERABILITY - 260°C FOR 3 SECONDS
DURABILITY - 600 CYCLES

ENVIRONMENTAL:

TEMPERATURE RANGE - -40°C TO +105°C

PACKING:

TUBE

FOR COMPLETE SPECIFICATION, SEE COMPONENT
SPECIFICATION C029XX (LATEST ISSUE).

NOTES:

- ALL TOLERANCES ARE ±0.25
UNLESS OTHERWISE STATED.

ORDER CODE:

M50-311XX42

No. OF WAYS PER ROW
05 TO 12, 15, 20, 25
30, 35, 40, 45 & 50

FINISH:

42 = SELECTIVE GOLD/100% TIN

RA	6	13.10.08	10175
NAME	ISS.	DATE	C/NOTE
APPROVED: <i>[Signature]</i>			
CHECKED: <i>[Signature]</i>			
DRAWN: J. KEIR			
CUSTOMER REF:			
ASSEMBLY DRG:			

HARWIN

HARWIN USA
TEL: 603 893 5376
FAX: 603 893 5396
mis@harwin.com

HARWIN Europe (UK)
TEL: 023 9231 4545
FAX: 023 9231 4590
mis@harwin.co.uk

HARWIN Asia
TEL: +65 6 779 4909
FAX: +65 6 779 3868
mis@harwin.com.sg

THIS DRAWING AND ANY
INFORMATION OR DESCRIPTIVE
MATTER SET OUT HEREON ARE
CONFIDENTIAL AND COPYRIGHT
PROPERTY OF THE HARWIN
GROUP AND MUST NOT BE
DISCLOSED, LOANED, COPIED
OR USED FOR MANUFACTURING,
TENDERING OR FOR ANY
OTHER PURPOSE WITHOUT
THEIR WRITTEN PERMISSION.

TOLERANCES
X. - ±1mm
X.X - ±0.25mm
X.XX - ±0.10mm
X.XXX - ±0.01mm
ANGLES - ±5°
UNLESS STATED

MATERIAL:

SEE ABOVE

FINISH:

SEE ABOVE

S/AREA:

mm²

TITLE:

1.27mm PITCH DIL SMT VERT.
SOCKET ASSEMBLY WITH POSTS

DRAWING NUMBER:

M50-311XX42

SHT
2
OF
2