

Datasheet

RS Pro Cable Mount MCX Connector Plug, 50 Ω Impedance, Crimp Termination, 0 to 6GHz, RG174/U cable type

RS Stock No: **738-5783**



Product Details

RS Pro cable mount MCX connector plug is suitable for operating frequencies ranging from 0 - 6 GHz. It is designed for 50 Ω impedance applications. This connector plug is compatible with RG174/U cable and offers crimp termination. The gold plated brass contact ensures superior connectivity.

Features and Benefits

- Suitable for applications such as mobile equipment and installations
- Gold plated brass contacts
- Nominal impedance 50 Ω

**Specifications:**

Body Orientation	Straight
Body Plating	Gold
Cable Type	RG174/U
Contact Material	Brass
Contact Plating	Gold
Gender	Male
Impedance	50 Ω
Mounting Type	Cable Mount
Operating Frequency	0 to 6 GHz
Termination Method	Crimp
Dimensions	15.8 x 5.5 mm
Operating Temperature Range	-55 to +155°C