


4				3	
DRAWING MADE IN THIRD ANGLE PROJECTION					
THIS DRAWING IS UNPUBLISHED.			RELEASED FOR PUBLICATION ,19 .		
© COPYRIGHT IS BY AMP INCORPORATED. ALL INTERNATIONAL RIGHTS RESERVED.					
AMP PART NO	MATERIAL	PKG TYPE	QTY		
8-36929-3	M/F 8-36929-0	BOX	25		
8-36929-5	M/F 8-36929-0	SPL	5		

LOC	DIST	P	F	REVISIONS				
G	14			ZONE	LTR	DESCRIPTION	DATE	APPO
					D	REVISED & REDRAWN PER 0720-0037-93	5/20/93	OK RER.



AMP WIRE RANGE	E13288 Listed
3/0 AWG SOLID OR STRANDED	3/0 AWG SOLID OR STRANDED
LR7189 Certified	MILITARY P/N AND CLASS
3/0 AWG SOLID OR STRANDED	NOT APPLICABLE

- 1 STAMP AMP 3/OW* APPROX AS SHOWN
- 2 STAMP 150 APPROX AS SHOWN
- 3 TONGUE MATERIAL THK: 2.31±0.08 [.091 ±.003]



								36929			
								PART NO			
AMP INCORPORATED CUSTOMER SERVICE SYSTEMS			MAX RECOMMENDED OPERATING TEMPERATURE: 170°C MAX		DO NOT SCALE PRINT. UNLESS SPECIFIED DIMENSIONS IN mm [INCHES] TOLERANCES ON: 2 PLC DEC ± 0.20[.008] 3 PLC DEC ± - ANGLES ± -		DR 5/20/93 OK SCHRUM		AMP Incorporated Harrisburg, PA 17105-3508		
FOR ADDITIONAL PRODUCT INFORMATION OR COPIES OF DRAWINGS AND TECHNICAL DOCUMENTS		PRODUCT INFORMATION CENTER 1-800-522-6752		VOLTAGE RATING: NOT APPLICABLE		MATERIAL COPPER ASTM B-152 ANNEALED		APPD 1/27/94 RE ROSER		NAME	
FOR APPLICATION TOOLING INFORMATION		TOOLING ASSISTANCE CENTER 1-800-722-1111		CIRCULAR MIL AREA: 76.3-96.3mm² [150,000-190,000] CIR MILS SOLID OR STRANDED		FINISH TIN PLATE 0.00254[.000100] MIN THK PER MIL-T-10727		APPD 1/27/94 JL MECKLEY		TERMINAL, RING TONGUE, SOLISTRAND™	
FOR ORDER ENTRY		1-800-526-5142		THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.				PRODUCT SPEC -		SIZE C	
								APPLICATION SPEC -		CAGE CODE 00779	
								WEIGHT -		DRAWING NO C-36929	
										SCALE 2:1	
										SHEET 1 OF 1	