




THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION
COPYRIGHT BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.

LOC		DIST		REVISIONS			
G		14		REV	DATE	OWN	APPD
				N	REV PER 0G3A-0319-03	27MAY03	JR TM



1. INSULATION DIA .170 MAX
2. FITS TAB .032 THK
- 3 PRELIMINARY — NOT FOR PRODUCTION

AMP WIRE RANGE	FILE E66717	LR7189 Certified
16-14 AWG STRANDED	16-14 AWG STRANDED	16-14 AWG STRANDED

3	LOOSE PC,BAG	8-640905-7
50	LOOSE PC,BAG	8-640905-6
5	LOOSE PC,BLS,SPL	8-640905-5
100	LOOSE PC,BOX	8-640905-1
1000	TAPE MOUNTED	640905-3
3500	TAPE MOUNTED	640905-2
1000	LOOSE PIECE	640905-1
QTY	PACKAGE TYPE	PART NO

AMP INCORPORATED CUSTOMER SERVICE SYSTEMS		MAX RECOMMENDED OPERATING TEMPERATURE: 105°C	THIS DRAWING IS A CONTROLLED DOCUMENT.		DWG L OLMEIDA 25JUN95	tyco Electronics Tyco Electronics Corporation Harrisburg, PA 17105	
FOR ADDITIONAL PRODUCT INFORMATION OR COPIES OF DRAWINGS AND TECHNICAL DOCUMENTS	PRODUCT INFORMATION CENTER 1-800-522-6752	VOLTAGE RATING: 300V MAX	DIMENSIONS: INCHES	TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 1 PLC ± - 2 PLC ± .015 3 PLC ± - 4 PLC ± - ANGLES ± -	CHK M ELLIS 26JUN95	NAME B BARE 25JUN95	RECEPTACLE, 250 SERIES, FASTON , PIDG , 16-14
FOR APPLICATION	TOOLING ASSISTANCE CENTER 1-800-722-1111	CIRCULAR MIL AREA: 2,050-5,180 STRANDED		MATERIAL BODY,BRASS .018	FINISH BODY,TIN	PRODUCT SPEC UL 310	SIZE A3
TOOLING INFORMATION	1-800-526-5142	THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING DEPARTMENT SHOULD BE CONTACTED FOR THE LATEST REVISION.				APPLICATION SPEC 114-1002	CAGE CODE 00779
FOR ORDER ENTRY	1-800-526-5142					WEIGHT -	DRAWING NO 640905
						CUSTOMER DRAWING	RESTRICTED TO -
						SCALE 6:1	SHEET 1 OF 1
							REV N