

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [19130-0044](#)
Status: **Active**
Description: BLOCK SPADE INSULKRIMP (B-2781-06X)

Documents:

Drawing (PDF)	Product Specification PS-19902-013 (PDF)
Product Specification PS-19902-009 (PDF)	RoHS Certificate of Compliance (PDF)
Product Specification PS-19902-011 (PDF)	

Agency Certification

CSA	LR18689
UL	E32244

General

Product Family	Ring and Spade Terminals
Series	19130
Crimp Quality Equipment	Yes
Product Family	Ring and Spade Terminals
UPC	800753101098

Physical

Flammability	94V-0
Net Weight	0.989/g

Material Info

Old Part Number	B-2781-06X
-----------------	------------

Reference - Drawing Numbers

Product Specification	PS-19902-009, PS-19902-011, PS-19902-013
Sales Drawing	SD-19130-003

EU RoHS

**ELV and RoHS
Compliant**
**REACH SVHC
Contains SVHC: No
Low-Halogen Status
Not Low-Halogen**

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
 For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

[19130Series](#)

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description	Product #
PremiumGrade™ Hand Crimp Tool	0640010100
Crimp Head for the AT-200™ Pneumatic Hand Tool	0640050100