

4

3

2

1

LOC	DIST	REVISIONS				
P	LTR	DESCRIPTION			DATE	APVD
					DWN	
	C	ECR-05-017969			17JAN06	JMS FWK

NOTES:

- 1

PACK IN ACCORDANCE WITH AMP SPEC 107-3275
- 2

100 TRAY PACK IN ACCORDANCE WITH AMP SPEC 107-3275
- 3

Au PLATING
- 4

Ni PLATING
- 5

ELECTRICAL CHARACTERISTICS

FREQUENCY RANGE:DC - 4 GHz

NOMINAL IMPEDANCE:50 Ohm

INSULATION RESISTANCE:5000 MOhm

WORKING VOLTAGE:500 Volts RMS at Sea Level

DIELECTRIC WITHSTAND VOLTAGE:1500 Volts RMS Max

CONTACT RESISTANCE:CENTRE CONTACT:1.50 mOhm Max




OUTER CONTACT:0.20 mOhm Max
- 6

MECHANICAL CHARATERISTICS

DURABILITY:500 Cycles Min
- 7

ENVIRONMENTAL CHARACTERISTICS

OPERATING TEMPERATURE:-65 to +165 DegC



		1	1	BRASS	4	FLANGE	5
		1	1	PTFE		INSULATION	4
		1	1	BRASS	3	CONTACT	3
		1	1	PTFE		INSULATION	2
		1	1	BRASS	4	BODY	1
		6--0	1--0	MATERIAL		DESCRIPTION	ITEM
		4	1				
QUANTITY PER ASSY				PARTS LIST			

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	J.SANDWELL	17JAN06	tyco Electronics Tyco Electronics Corporation Bideford EX39 4HE		
DIMENSIONS: mm		CHK	S.PARLOW	17JAN06			
		APVD	F.WHEELER-KING	17JAN06	NAME		
		PRODUCT SPEC			BNC PANEL SOCKET 50 OHM		
MATERIAL		APPLICATION SPEC			SIZE		
		WEIGHT			CAGE CODE		
SEE TABLE		CUSTOMER DRAWING			DRAWING NO		
					RESTRICTED TO		
					SCALE		
					SHEET		
					REV		