

RACD20/277

LED DRIVER

RECOM
LIGHTING



RATED POWER

20W max.

FEATURES

- Power Factor Corrected
- IP66 Rating
- Low Cost

CERTIFICATION	INPUT	DIMMING	PROTECTION	OUTPUT	CC ✓	CV
CE ✓	115VAC ✓	0-10V X	Over-Voltage ✓	RACD20-350/277	350mA	28-57VDC
UL ✓	230VAC ✓	PWM X	Short-Circuit ✓	RACD20-500/277	500mA	20-40VDC
EN ✓	277VAC ✓	Resistor X	Over-Load ✓	RACD20-700/277	700mA	14-29VDC
EMC ✓	AC or DC ✓	Triac Dimming X	Over-Temp. ✓	RACD20-1050/277	1050mA	18.8-19VDC

MECHANICAL CHARACTERISTICS

Size	80 x 74 x 26.5mm
Weight	195g
Connection	Wires

TEMPERATURE CHARACTERISTICS

Operating Temperature	-20°C to +50°C
Case Temperature (Tc)	+90°C max.

INSTALLATION

