

Product Lineup

Photo Base Paper

Premium Plus Photo Paper Professional



Perfect for people emphasizing quality

Quality Grade	★★★★★
Type	Photo Base Paper
Weight	270gsm
Surface	Extra Glossy
Size*	A3(20) / A4(20) / 10x15cm(20, 50)



Perfect for anniversaries

Quality Grade	★★★★★
Type	Photo Base Paper
Weight	270gsm
Surface	Satin
Size*	A3(20) / A4(20) / 10x15cm(20)

Premium Plus Photo Paper



Perfect for presents

Quality Grade	★★★★★
Type	Photo Base Paper
Weight	235gsm
Surface	Super Glossy
Size*	A4(20, 50) / Letter(20) / 10x15cm(20, 50, 100)

*Numbers in parentheses after size denote the numbers of sheets per package.

Cast Coated Paper

Photo Quality Paper



Perfect for presentations and POP productions

Quality Grade	★★★★★
Type	Cast Coated Paper
Weight	190gsm
Surface	Glossy
Size*	A4(20, 50) / Letter(20) / 10x15cm(20, 50)

Regular Photo Paper



Perfect for printing in large quantities

Quality Grade	★★★★★
Type	Cast Coated Paper
Weight	150gsm
Surface	Glossy
Size*	A4(100) / 10x15cm(100)

*Numbers in parentheses after size denote the numbers of sheets per package.

Product Comparison

	Weight	Surface	Type	Size (Number of sheets)				Quality Grade
				A3	A4	Letter	10x15cm	
Premium Plus Photo Paper Professional	270gsm	Extra Glossy	Photo Base Paper	● (20)	● (20)		● (20/50)	★★★★★
Premium Plus Photo Paper Professional	270gsm	Satin	Photo Base Paper	● (20)	● (20)		● (20)	★★★★★
Premium Plus Photo Paper	235gsm	Super Glossy	Photo Base Paper		● (20/50)	● (20)	● (20/50/100)	★★★★★
Photo Quality Paper	190gsm	Glossy	Cast Coated Paper		● (20/50)	● (20)	● (20/50)	★★★★
Regular Photo Paper	150gsm	Glossy	Cast Coated Paper		● (100)		● (100)	★★★

