



Sample photo

Order symbol: PC B 65 G
Product nbr: 8724303
Description: Enclosure, PC
Remarks: Grey cover

EAN: 6418074001955
El. number:
Finland: 3423401
Electric No. Denmark: 8212001475
Electric No. Italy: 7201010
Electric No. Sweden: 2536801

Including: Base with screws for mounting plate/DIN-rail, cover with PUR gasket and polyamide cover screws.

Dimensions:			Accessories:	
mm:	110	80	65	B-3 DIN-35 Mounting rail
inch:	4.3	3.1	2.6	FP 22040 Wall fastening lug (2 pcs)
Materials:			Rating:	
Material:	Polycarbonate		Ingress Protection (EN 60529): IP66/67	
Base colour:	RAL 7035 -light grey		Impact Resistance (EN 62262): IK08	
Cover screws material:	Polyamide		Electrical insulation: Totally insulated	
Cover colour:	RAL 7035 -light grey		Halogen free (DIN/VDE 0472, Part 815): 1	
Cover screws colour:	Grey		UV resistance: UL 508	
Gasket material:	Polyurethane		Flammability Rating: UL 746C 5V	
			Glow Wire Test (IEC 695-2-1) °C: 960	
			NEMA Class: NEMA 1, 4X, 6, 6P, 12, 13	
Temperatures:			Certificates:	
Temperature °C (short term):	-40 ... 120 °C		Germanischer Lloyd (GL)	
Temperature °C (continuous):	-40 ... 80 °C		SGS Fimko	
Temperature °F (short term):	-40 ... 250 °F		Gost R	
Temperature °F (continuous):	-40 ... 175 °F			
Accessories:				
B-MP	Mounting plate			

PICCOLO 110x80x65-85

