

Datasheet

RS Pro Black Loop, 22mm

RS Stock No: **890-4196**



Product Details

RS Pro die-cut coin-shaped hook and loop tape in black colour, has a rubber-based adhesive coating on the back of the loop coin for instant bonding on variety of surfaces. This coin-shaped loop pieces are supplied on a clear poly-liner roll for easy application. The loop coin is 22 mm wide.

Features and Benefits

- Die-cut coin-shaped self adhesive loop coins
- Rubber-based adhesive coating
- Supplied on a clear poly-liner roll for easy application
- Provides an instant bond to a variety of surfaces including glass, metal, wood and plastic
- 22 mm wide



ENGLISH

Specifications:

Colour	Black
Format	Coin
Hook Type	Loop
Length	5 m
Width	22 mm



Adhesive Coins

A high tack hot-melt rubber based adhesive system, coated to the back of hook & loop tape offering instant bond to most surfaces.

Adhesive colour: Light Yellow

Performance: A strong instant bond

Typical Application: Immediate adhesion to a variety of surfaces including paper, wood, polythene, metal, glass, plastic etc. (excluding plasticised PVC).

Material: Base (backing)	80% Nylon/20%PE
Material: Hooks & Loops	80% Nylon/20%PE
Weight:	360g/m ²
Peel strength	3.5N/cm
Shear strength	18N/cm ²
Hooks per square inch	300
Loops per square inch	330

Not recommended for direct exposure to sunlight & U.V.

Application Guide: To be avoided on surfaces of humidity, dust, oil etc. Application temperature from +5 to +40 degree C.