

Conductor marker - UC-WMC 3,1 (15X 4) - 0818205

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)

Conductor marker, Sheet, white, Unlabeled, Can be labeled with: Bluemark, Plotter, BLUEMARK CLED, Mounting type: Clip on, Cable diameter: 1.9-3.1 mm, Lettering field: 15 x 4 mm



Why buy this product

- The UC-WMC ... UniCard labeling range includes markers for captive labeling of control lines to cable sheaths with large diameters
- Can be clipped on even after wiring has been completed
- One-handed assembly
- Two labeling areas that are clearly legible at all times
- The markers, which are supplied in uniform sheets, can be labeled quickly and easily using the BLUEMARK LED
- Labeling service: Phoenix Contact can custom-label all UniCard markers according to your requirements
- The sheets provide space for including function texts
- The markers support multi-line labeling
- The format automatically ensures printing with a high degree of positioning accuracy

Key commercial data

| | |
|------------------------|---|
| Packing unit | 0 |
| Minimum order quantity | 10 |
| Catalog page | Page 137 (CL2-2011) |
| GTIN |  4 046356 133531 |
| Custom tariff number | 39269097 |
| Country of origin | POLAND |

Technical data

General

| | |
|---|--------------------------------|
| Width (a) | 15 mm |
| Color | white |
| Inflammability class according to UL 94 | V2 |
| Wipe resistance | DIN EN 61010-1 (VDE 0411-1) |
| Ambient temperature (operation) | -40 °C ... 120 °C |
| Components | free from silicone and halogen |
| Material | PA |
| Number of individual labels | 20 |
| Number of individual labels per row | 4 |

Conductor marker - UC-WMC 3,1 (15X 4) - 0818205

Classifications

ETIM

| | |
|----------|----------|
| ETIM 2.0 | EC000761 |
| ETIM 3.0 | EC000761 |
| ETIM 4.0 | EC000761 |
| ETIM 5.0 | EC001530 |

UNSPSC

| | |
|---------------|----------|
| UNSPSC 11 | 39121410 |
| UNSPSC 12.01 | 39121410 |
| UNSPSC 13.2 | 39121410 |
| UNSPSC 6.01 | 30211811 |
| UNSPSC 7.0901 | 39121410 |

eCl@ss

| | |
|------------|----------|
| eCl@ss 4.0 | 24190219 |
| eCl@ss 4.1 | 24190219 |
| eCl@ss 5.0 | 27149103 |
| eCl@ss 5.1 | 27400401 |
| eCl@ss 6.0 | 27400401 |
| eCl@ss 7.0 | 27400401 |

Accessories

Accessories

Magazine - P1 UC-MAG 1 - 5146079



Magazine, for CMS-P1-PLOTTER, for accommodating UC-TM..., UC-TMN..., UC-WMC 3.1..., UC-WMTBA...