

Datasheet

Cross Connector

RS Stock number 872-4773



Cross-connection
insulated

Description:

The SQI cross-connections for the screw connection system have a pluggable, insulated design. They can be used to conduct the rated current of the corresponding cross-section range. The terminal block design and the variability of the cross-connector ensure excellent flexibility.

Specifications:

Rated current, A Max. current, A:	57 76
Max. voltage with partition plate, V:	1000
Max. voltage without partition plate, V:	1000
Rated impulse voltage, kV Contamination degree:	- 3
Pitch, mm:	10