

Datasheet

Stock No: 811-4390

# RS Pro 4 Core Unscreened White 3184Y Power Cable



Conductors	50/0.25mm Plain Annealed Copper (Class 5 to IEC 60228)
Insulation	PVC (Type T11 to BS 7655)
Insulation Radial Thickness	0.80mm
Diameter over Insulation	3.65mm (Nominal)
Number of Cores	4
Core Colours	Brown, Black, Grey & Green/Yellow
Sheath	PVC (Type TM2 to BS 7655)
Sheath radial thickness	1.10mm
Overall Dimensions	11.03mm (Nominal)
Voltage Rating	300/500V
Conductor Resistance	7.98 $\Omega$ /km at 20°C (Nominal)
Cable Weight	215 kg/km (Nominal)
Standards	BS EN 50525-2-11 Table 4.2
Harmonization Code	H05VV-F
Sheath Colour	White
Reel Length	100m