

Datasheet

RS Green/Yellow Equipment Wire, 2491X, 2.5 mm² CSA , 750 V 25 A, 100m

Stock number: 544-1793



Description:	50/0.25mm. PCW x 0.8mm. single PVC insulated.
Conductor	(2.5mm ²) 50/0.25mm plain annealed copper.
Insulation	0.8mm nominal thickness, to 4.1mm upper limit.
Standard	BS6004: 2000 Table 4.
Voltage rating	450/750 V.
Conductor res.	7.98 Ω/1000mts.
Spark test	6000 volts rms.
Temperature Rating	70°C

Voltage ratings:	
between conductor and earth	300V (0.5 to 1mm ²)
	450V (1.5 to 2.5mm ²)
between conductors	500V (0.5 to 1mm ²)
	750V (1.5 to 2.5mm ²)