



Back to search results

62285

This part is in stock!


Inventory Snapshot:	56 feet*
----------------------------	----------

*Material in stock maybe allocated to other orders and is subject to prior sales


OEM Pricing*

8 feet: \$93.75 per foot	16 feet: \$48.76 per foot	32 feet: \$36.74 per foot
---------------------------------	----------------------------------	----------------------------------

*For larger quantities, please contact our sales department

	Part Number	Thermal Resistance °C/W at 3in length*	Width in	Height in	Surface Area in ² /in	Weight lb/ft	Part Class
	62285	1.23	6.75	1.63	56.9	4.00	A

*Based on a 75°C rise in natural convection



Thermal Curves


based on 3.000 in length

New Length ☒ in ☐ mm


Change Length



Natural Convection

Heat Sink Temperature Rise Above Ambient



Heat Sink Thermal Resistance






Forced Convection


Heat Sink Temperature Rise
Above Ambient (25W Dissipated)



Air Flow (m/s)



Heat Sink
Thermal Resistance

Air Flow (m/s)





Building a Part Number

Full Bar Length = 8.00ft

Base Part #	Bar Length	Finish	Length (use zeros for full or half bars)	RoHS
5 digit base part #	<u>1</u> Full (normally 8-ft)	<u>E</u> Unfinished	0 0 0 0 0	Compliant NO "G" required
	<u>2</u> Half (small cut fee)	<u>E</u> Unfinished	0 0 0 0 0	
	<u>3</u> Custom (cut to specified length)	<u>B</u> Black Anodized	length in inches to three decimal places**	Compliant Add "G"
		<u>U</u> Unfinished*		
		<u>V</u> AavSHIELD ³		
		<u>C</u> Gold Chromate		Not Compliant

62285
3
U
06500
G

*For unfinished extrusions with cut lengths other than half bar, the finish designation is a U.

**If the part is less than 10 inches, the first of these 5 digits (digit 7 of the 13 digit series) would be a zero (0).

Examples:

If you wanted to simply order extrusion # 62285 in standard bar form, the part number would be: 622851F00000. The unit price would be sold by the foot.

If you wanted extrusion 62285 cut to a length of 6.500" and black anodized, the part number would be: 622853B06500G. The unit price would be by the piece.

If you wanted extrusion 62285 cut to a length of 14.725" and a wash finish, the part number would be: 622853U14725G. The unit price would be by the piece.

If you wanted extrusion 62285 cut to a length of 14.725" and Gold Chromate finish, the part number would be: 622853C14725. The unit price would be by the piece.

Standard Aavid Thermalloy parts require all 12-13 positions to be complete.

Non-Standard Extrusions

Aavid Thermalloy has over 10,000 extrusion profile designs on file, most with the extrusion die already available. These parts have minimum order requirements and longer lead times, but may be cost effective compared to a new design.

Customizing & Advanced Capabilities

We offer several options for those applications which require a more unique solution. Challenge us with your thermal requirements - we can design custom solutions.

©2012 Aavid Thermalloy, LLC