



ENGLISH

Datasheet

Stock No: 285-8801

RS Pro 22mm x 3/4 in BSPP Female 90° Wall Plate Elbow Adapter Brass Compression Fitting



Product Details

Wall Plate Fitting

Wall plate flange has two fixing holes
Female Thread is BSP parallel

Note

See 'Key characteristics' table for guide to pressure/temperature.

Fittings - Chrome Plated Brass

Chromium plated brass fittings.

Type A fittings suitable for mechanically joining metric o/d tubing in accordance with: Copper tube to BS2871: Part 1: Table X Table Z. Stainless steel tube to BS4127: Part 2: 1972.

For suitable chromium plated copper tube

BS864/2 BSI Kitemark Licence no. KM07082



ENGLISH

Key Characteristics			
Medium	Service Temperature up to	Max. Working Pressure	
	°C	BAR	PSI
Water or light mineral oils 8 to 54mm sizes	30	16	230
	65	10	145
	110	6	87
	120	5	75
Compressed air non-shock 8 to 28mm sizes only	30	7	100
Saturated steam	120	3	4545
LPG & Natural Gas 8 to 28mm sizes only	30	1	15

Specifications:

Compression Connection Pipe Diameter	22mm
Fitting Type	Wall Plate Elbow Adapter
Material	Brass
Threaded Connection	3/4 in BSPP Female
Fitting Direction	90°
Thread Size	3/4in
Thread Standard	BSPP
Gender	Female