

new Kübler Codix 907 | Kübler Codix 908

The simple, economical, high-performance Preset Counter

Counters and Process Displays

Position and Motion sensors

Connectors and Transmission technology

OEM products and OEM systems

Kübler → Counting technology → Preset counters → electronic



Quality brand – Made in Germany

For Pulses, Time, and Position

Menu-driven programming

Plug-in screw terminals

High-quality LCD display

3-year warranty

Kübler Codix 907 | Kübler Codix 908



Pulses
Time
Position



Presets
907:1
908:2



2 x 6 LCDs



Supply voltage
11 ... 30V



115 / 230V



DIN front-panel
DIN 48 x 48



Plug-in screw terminal



High IP value
IP 65



Temperature range
-10° +50°



Count frequency
typ. 5 kHz



Menu-driven programming



RoHS compliant

Simple

- Plug-in screw terminals
- Menu-driven programming
- Decade keypad
- DC or AC
- Minimum installation depth
- High protection rating (IP65) with integrated gasket for front panel
- With preset annunciators

Economical

- Modern technology platform
- Slimmed-down to essential functions
- Modular system principle

High-performance

- For pulses, time, and position
- Adding and subtracting
- Automatic reset, via key or electrical
- 1 preset: Kübler Codix 907
- 2 presets: Kübler Codix 908
- 2 x 6-digit display with preset annunciators from -999999 up to +999999
- With or without backlighting

