



PART No.	THREAD A	NOMINAL DIMENSIONS (mm)					
		B	C	D	E	F	G
AT13/M16/CS90/*	M16x1.5	12.0	44.3	21.2	11.0	24.0	65.2
AT16/M16/CS90/*	M16x1.5	12.0	44.3	23.2	11.0	24.0	65.2
AT21/M20/CS90/*	M20x1.5	12.0	47.5	30.2	15.4	27.0	70.0
AT28/M25/CS90/*	M25x1.5	12.3	57.5	37.2	19.0	34.0	76.4
AT34/M32/CS90/*	M32x1.5	17.0	70.3	44.2	25.9	42.0	86.4
AT42/M40/CS90/*	M40x1.5	17.5	87.5	54.2	33.3	52.0	104.7
AT48/M50/CS90/*	M50x1.5	16.0	110.7	65.0	43.8	63.0	127.6
AT54/M50/CS90/*	M50x1.5	16.0	110.7	66.2	43.6	70.0	127.6
AT54/M63/CS90/*	M63x1.5	16.0	110.7	66.2	43.6	70.0	127.6

* SPECIFY COLOUR OPTION
 BLY BLACK/YELLOW
 BLB BLACK/BLUE
 GRY GREY/YELLOW
 GRB GREY/BLUE



BIRMINGHAM ENGLAND

This drawing/document is a COPYRIGHT and the property of CABLE MANAGEMENT PRODUCTS LTD. It must not be copied (in whole or part) used for manufacture or otherwise disclosed without prior written consent of the company. The Company's policy is one of continuous improvement and it therefore reserves the right to change specifications at any time without notice.

MATERIAL PA66/TPV/BRASS

FINISH FINE SPARK

METRIC THREADS

DATE 31/10/07

CHARTS ATS-CS90-METRIC

TITLE

ADAPTALOK ATS
 TYPE CS90
 IP68 FITTINGS