

Datasheet

RS Pro 50 Ω Right Angle Cable Mount MMCX Connector, Plug, Crimp Termination, RG178/U

RS Stock No: **655-9968**



Product Details

RS Pro PCB mount MMCX connector jack is designed for 50 Ω impedance applications. This right angle connector jack offers crimp termination and includes PTFE dielectric, gold plated brass body and contacts for superior connectivity. It is suitable for use with RG178 and RG174 RF coaxial cable types. The snap on mechanism gives flexibility in PCB layouts by allowing for 360° rotation.

Features and Benefits

- DC to 6 GHz frequency range
- Available in cable, panel and PCB mount versions
- Low RF leakage

Specifications:

Body Orientation	Right Angle
Body Plating	Gold
Cable Type	RG178/U
Contact Material	Brass
Contact Plating	Gold
Gender	Male
Impedance	50 Ω
Mounting Type	Cable Mount
Operating Frequency	0 to 6 GHz
Size	Micro Miniature
Termination Method	Crimp
Dimensions	7.9 x 7 mm
Operating Temperature Range	-55 to +165°C
Voltage Rating	170 V