

60 - 100kg

Institutional Castors Series 2470

Housing made of pressed steel, bright zinc plated, blue passivated, double ball bearing swivel head, wheel axle with nut
 Drawings of plate fittings see on page 38-39
 Load capacity tested according EN 12530



	Wheel diameter [mm]	Width of Tread [mm]	Size of Plate [mm]	Plate hole centres [mm]	Plate hole [mm]	Offset [mm]	Overall height [mm]	Load capacity [kg]	Express / On Stock	Order number	EAN Code
Swivel Castors											
	75	25	60 x 60	48/38 x 48/38	6,3	24	100	60		2470PIP075P40	4031582361230
	75	25	60 x 60	48/38 x 48/38	6,3	24	100	75		2470PJP075P40	4031582010466
	100	32	77 x 67	61,5/56 x 51,5/46,5	8,5	38	135	80		2470PIP100P50	4031582361278
	100	32	77 x 67	61,5/56 x 51,5/46,5	8,5	38	135	100		2470PJP100P50	4031582010480
	125	32	77 x 67	61,5/56 x 51,5/46,5	8,5	41	160	80		2470PIP125P50	4031582361339
	125	32	77 x 67	61,5/56 x 51,5/46,5	8,5	41	160	100		2470PJP125P50	4031582010503
	150	32	77 x 67	61,5/56 x 51,5/46,5	8,5	45	185	80		2470PIP150P50	4031582361391
150	32	77 x 67	61,5/56 x 51,5/46,5	8,5	45	185	100		2470PJP150P50	4031582010756	
Fixed Castors										Order number	EAN Code
	75	25	67 x 60	48/40 x 48/40	6,3		100	60		2478PIP075P60	4031582362220
	75	25	67 x 60	48/40 x 48/40	6,3		100	75		2478PJP075P60	4031582302400
	100	32	77 x 67	61,5/56 x 51,5/46,5	8,5		135	80		2478PIP100P50	4031582362237
	100	32	77 x 67	61,5/56 x 51,5/46,5	8,5		135	100		2478PJP100P50	4031582030365
	125	32	77 x 67	61,5/56 x 51,5/46,5	8,5		160	80		2478PIP125P50	4031582362244
	125	32	77 x 67	61,5/56 x 51,5/46,5	8,5		160	100		2478PJP125P50	4031582030389
	150	32	77 x 67	61,5/56 x 51,5/46,5	8,5		185	80		2478PIP150P50	4031582362251
150	32	77 x 67	61,5/56 x 51,5/46,5	8,5		185	100		2478PJP150P50	4031582030631	
Swivel Castors with total lock										Order number	EAN Code
	75	25	60 x 60	48/38 x 48/38	6,3	24	100	60		2477PIP075P40	4031582362008
	75	25	60 x 60	48/38 x 48/38	6,3	24	100	60		2477PJP075P40	4031582050431
	100	32	77 x 67	61,5/56 x 51,5/46,5	8,5	43,5	135	80		2477PIP100P50	4031582362046
	100	32	77 x 67	61,5/56 x 51,5/46,5	8,5	43,5	135	100		2477PJP100P50	4031582050455
	125	32	77 x 67	61,5/56 x 51,5/46,5	8,5	41	160	80		2477PIP125P50	4031582362091
	125	32	77 x 67	61,5/56 x 51,5/46,5	8,5	41	160	100		2477PJP125P50	4031582050479
	150	32	77 x 67	61,5/56 x 51,5/46,5	8,5	36	185	80		2477PIP150P50	4031582362145
150	32	77 x 67	61,5/56 x 51,5/46,5	8,5	36	185	100		2477PJP150P50	4031582050691	
Swivel Castors with directional lock										Order number	EAN Code
	100	32	77 x 67	61,5/56 x 51,5/46,5	8,5	43,5	135	80		2471PIP100P50	4031582361506
	100	32	77 x 67	61,5/56 x 51,5/46,5	8,5	43,5	135	100		2471PJP100P50	4031582301410
	125	32	77 x 67	61,5/56 x 51,5/46,5	8,5	41	160	80		2471PIP125P50	4031582361520
	125	32	77 x 67	61,5/56 x 51,5/46,5	8,5	41	160	100		2471PJP125P50	4031582301434
	150	32	77 x 67	61,5/56 x 51,5/46,5	8,5	36	185	80		2471PIP150P50	4031582361544
	150	32	77 x 67	61,5/56 x 51,5/46,5	8,5	36	185	100		2471PJP150P50	4031582301458

<p>Wheel: PJP Wheel centre: Polypropylene, Tread: TENTEprene (thermoplastic rubber), with threadguards, precision ball bearing</p>	<p>Wheel: PIP Wheel centre: Polypropylene, Tread: solid rubber, grey, non-marking, with threadguards, precision ball bearing</p>	<p>Optional wheel: DIK Wheel centre: pressed steel, Tread: rubber, grey, non-marking, with threadguards, cone ball bearing</p>	<p>Optional wheel: DYK electric conductive and according to ESD Wheel centre: pressed steel, Tread: rubber tyre, black, non-staining, with threadguards, cone ball bearing</p>
--	--	--	--