

General Information

Extended Product Type:	4125RS6W
Product ID:	2CMA167264R1000
EAN:	7392696672641
Catalog Description:	Surface socket-outlet, 6h, 125A, IP67, 3P+N+E
Long Description:	Surface socket-outlet, earthing sleeve position 6h, rated current 125A, IP67 watertight, 3-poles+neutral+earth, frequency 50-60 Hz, color code Red

Categories

Products » Low Voltage Products and Systems » Industrial Plugs and Sockets » Plugs & Sockets » Surface Socket Outlets

Ordering

EAN:	7392696672641
Minimum Order Quantity:	1 piece
Country of Origin:	Czech Republic (CZ)

Dimensions

Product Net Width:	145 mm
Product Net Height:	282 mm
Product Net Length:	171 mm
Product Net Depth:	282 mm
Product Net Weight:	1.69 kg

Container Information

Package Level 1 Width:	179 mm
Package Level 1 Length:	370 mm
Package Level 1 Height:	152 mm
Package Level 1 Gross Weight:	1.83 kg
Package Level 1 EAN:	7392696672641
Package Level 1 Units:	1 piece

Environmental

RoHS Status:	Planned to follow EU Directive 2002/95/EC August 18, 2005 and amendment after 2006-03-01
--------------	--

Certificates and Declarations (Document Number)

Declaration of Conformity - CE:	2CMC700005D0001
Environmental Information:	2CMC700001D0002
RoHS Information:	2CMC700057D0001

Additional Information

Additional Information:	Cable entry Ø50mm
Cable Cross-Section:	16 ... 70 mm ²
Color:	Red
Degree of Protection:	IP67
Enclosure Material:	Thermoplastic polyester (PBT)
Frequency (f):	50 Hz 60 Hz
Function:	Surface socket outlet
IIT Publishing Status:	Level 0 - Information enabled
Invoice Description:	Ind. P&S#4125RS6W
Number of Poles:	5
Object Classification Code:	2CMT005069
Product Main Type:	RS
Product Name:	Industrial Socket Outlet
Protection Type:	Watertight
Rated Current (I _n):	125 A
Rated Voltage (U _r):	346 ... 415 V
RoHS Date:	L23
Standards:	IEC 60309-1,-2
Suitable For:	Surface Socket Outlets

Suitable for Product Class: Industrial Plugs and Sockets

Classifications

E-nummer: 2416597

UNSPSC: 39120000

