

PATG 2/10


Order No.: 1013818

The illustration shows version PATG 0/15



Conductor marker carrier, closed, 10 mm wide, conductor diameter 2.0
- 4.0 mm

Commercial data

EAN	 4 017918 014001
Pack	1000
Customs tariff	39269098
Country of Origin	IT
Catalog page information	Page 190 (CL2-2011)

Product notes

WEEE/RoHS-compliant since:
01/01/2005



Please note that the data given here has been taken from the online catalog. For comprehensive information and data, please refer to the user documentation at <http://www.download.phoenixcontact.com>. The General Terms and Conditions of Use apply to Internet downloads.

Technical data**General**

Width (a)	10 mm
Color	transparent
Inflammability class acc. to UL 94	V0
Ambient temperature (operation)	-50 °C ... 80 °C

Components	Silicone-free
Material	PVC
