

# elite 404 Wallbox

The versatile and cost-effective wall mounted enclosure from



The 404 Wallbox is the latest addition to the Elite range. This cost-effective stylish wall mounted enclosure is designed to the highest standards as you would expect from an Elite product. As with the whole of the Elite range, the 404's design is based on input from you the user - which is probably why it features everything that you'd want to see as standard in a wall mounted enclosure.

## FEATURES

- 4 heights and 2 depths – available as 450mm deep front section or as 550mm deep 2 part wall box. The front section can be rotated to hinge left or right and swing out to 90° for easy access. A single key point secures the front to the rear section (2 keys supplied).
- Adjustable 19" mounting angles provide cable management space in front and cable access around both sides of the 19" angles
- Quick cable access is achievable via the unique clip-on plastic gland plates which snap quickly and easily in to the top and bottom glands.
- Rear section incorporates top and bottom metal gland plates for additional access.
- Lockable glass or steel doors which can be hung left or right with our quick reverse facility.
- Pre-punched patterns in top and base assist with air flow and circulation
- Retro-fitable 2 way top or bottom fan tray option which takes up no additional U space.
- Integral mounting positions for power distribution units (19", horizontal or vertical), cable trays and cable tie points.
- A strong yet lightweight welded frame, giving a load rating of 50kg.
- Door acts as a template for quicker installation.

elite/form meets function



# elite 404 Wallbox

## SPECIFICATION

<b>Construction:</b>	Single and rear sections welded 1mm & 1.2mm steel 4mm toughened glass
<b>Load rating:</b>	50kg
<b>Colour:</b>	Slate Grey & Goose Grey
<b>Mounting angles:</b>	1.5mm steel

## ONE PART 404 WALLBOX

U Height	Glass Door	Steel Door	Actual Height	Width	Depth
6	WB2-006-300	WB2-076-300	322mm	600mm	450mm
10	WB2-010-300	WB2-080-300	500mm	600mm	450mm
14	WB2-014-300	WB2-084-300	677mm	600mm	450mm
18	WB2-018-300	WB2-088-300	855mm	600mm	450mm

## TWO PART 404 WALLBOX

U Height	Glass Door	Steel Door	Actual Height	Width	Overall Depth
6	WB2-056-300	WB2-116-300	322mm	600mm	550mm
10	WB2-060-300	WB2-120-300	500mm	600mm	550mm
14	WB2-064-300	WB2-124-300	677mm	600mm	550mm
18	WB2-068-300	WB2-128-300	855mm	600mm	550mm

DESCRIPTION	PARTS NO:	CONTENTS/SIZE
6u 19" Mounting Angle Kit (404)	GA1-580-311	Comprises pair angles & fixings
10u 19" Mounting Angle Kit (404)	GA1-581-311	Comprises pair angles & fixings
14u 19" Mounting Angle Kit (404)	GA1-582-311	Comprises pair angles & fixings
18u 19" Mounting Angle Kit (404)	GA1-583-311	Comprises pair angles & fixings
6u ETSI Mounting Angle Kit (404)	GA1-590-311	Comprises pair angles & fixings
10u ETSI Mounting Angle Kit (404)	GA1-591-311	Comprises pair angles & fixings
14u ETSI Mounting Angle Kit (404)	GA1-592-311	Comprises pair angles & fixings
18u ETSI Mounting Angle Kit (404)	GA1-593-311	Comprises pair angles & fixings
Flat Bar Jumper Rings	BI1-206-101	45 x 60mm
Flat Bar Jumper Rings	BI1-207-101	60 x 60mm
Horizontal 1u Jumper Ring Panel	GA1-083-312	Complete with fixings
Cable tie bar	SM1-180-321	465mm
Earth Bonding Kit	EA1-024-000	270mm earth wires
Gland Plate (404)	PMD00140000A0000	155x155mm Slate Grey (no fixings required)
PDU Bracket (404)	GA1-550-311	Complete with fixings
Fan tray – Top or Bottom fitting	EA1-133-021	2 x fans 120mm sq x 25mm deep AC fans 78/84m/Hr 110-240v
Cantilever Shelf	SM1-345-310	1u 200mm deep
Cantilever Shelf	SM1-346-310	1u 300mm deep
Cantilever Shelf	SM1-349-310	2u 400mm deep
Cable Tidy Shelf	GA1-202-311	2u 400mm deep
Chassis Runners (needs additional mounting angles fitting to rear)	GA1-600-311	Comprises one pair & fixings
Fixed Shelf (needs additional mounting angles fitting to rear)	GA1-560-311	350mm deep