

## Datasheet

### Switchgear Cable

8114551  
5167928  
8114542  
5167906  
8114554  
5167956  
8114558  
5167934  
8114567  
5167940



**Conductor:** 84/0.30mm Plain Annealed Copper (Class 5 to IEC 60228)

**Insulation:** PVC (Type TI1 to BS EN 50363)

**Insulation Radial Thickness:** 0.80mm

**Diameter Over Insulation:** 5.30mm (Maximum)

**Voltage Rating:** 600/1000V

**Conductor Resistance:** 3.3  $\Omega$ /km @ 20°C (Nominal)

**Cable Weight:** 70.80 kg/km (Nominal)

**Standard:** BS 6231:2006