

## Sleeve frame - VC-TR2/3M - 1852901

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)

Sleeve frame, without PE, for contact insert modules, type 2, number of insert modules 3



The illustration shows the version VC-TR 1/2 M



### Key commercial data

Packing unit	5 pc
Minimum order quantity	5 pc
GTIN	 4 017918 133740
Weight per Piece (excluding packing)	9.16 g
Custom tariff number	85389099
Country of origin	Poland

### Technical data

#### Dimensions

Height	27.5 mm
Width	65.2 mm

#### Ambient conditions

Ambient temperature (operation)	-40 °C ... 100 °C
---------------------------------	-------------------

#### General

Type	VC2
Color	black
Material	PA-GF
Housing material	Plastic
Inflammability class according to UL 94	V0

# Sleeve frame - VC-TR2/3M - 1852901

## Classifications

### eCl@ss

eCl@ss 4.0	27140816
eCl@ss 4.1	27140816
eCl@ss 5.0	27189239
eCl@ss 5.1	27189239
eCl@ss 6.0	27144001
eCl@ss 7.0	27144001
eCl@ss 8.0	27144001

### ETIM

ETIM 2.0	EC000007
ETIM 3.0	EC000007
ETIM 4.0	EC000007
ETIM 5.0	EC000007

### UNSPSC

UNSPSC 6.01	43172601
UNSPSC 7.0901	31261501
UNSPSC 11	43172601
UNSPSC 12.01	31261501
UNSPSC 13.2	31261501

## Approvals

### Approvals

---

#### Approvals

UL Recognized / cUL Recognized / cULus Recognized

---

#### Ex Approvals

---

Approvals submitted


---


### Approval details

UL Recognized 
---

## Sleeve frame - VC-TR2/3M - 1852901

### Approvals

cUL Recognized 

cULus Recognized 

### Drawings

Dimensioned drawing

