


Datasheet

RS Cable Assembly 200mm, DIN to USB A x 2

Stock Number: 294-9474



Connector A	Female USB A x 2
Connector A Type	USB A x 2
Connector B	Female DIN
Connector B Type	DIN
Length	200mm



REVISIONS			
DATE	LTR	DESCRIPTION	APPR.
07/11/2005	A	NEW RELEASE	
07/11/2005	B	RUNNING CHANGE	

SPECIFICATION
 1.100% OPEN-SHORT TEST.
 2.INSULATION RESISTANCE >2MΩ DC300V 0.01SEC.
 3.CONTACT RESISTANCE <0.9Ω

PIN ASSIGNMENT

CONDUCTOR	COLOR	FUNCTION
P2	RED	P1
1	WHITE	9
2	GREEN	7
3	BLACK	5
4	DRAIN	3
SHELL		1
P3	RED	2
1	WHITE	4
2	GREEN	6
3	BLACK	8
4	DRAIN	10
SHELL		

ITEM	MATERIAL	SPECIFICATION	UNIT	QTY
12	TERMINAL	BRASS GOLD PLATED	PCS	10
11	HOUSING	2x5PIN HSG, 2.54MM PITCH(COLOR: BLACK)	PC	1
10	H. S. T.	HEAT SHRINK TUBE Ø1.0x35MM (COLOR: BLACK)	PC	1
9	H. S. T.	HEAT SHRINK TUBEØ9.0x15MM (COLOR: BLACK)	PC	2
8	NUT	5.4x2.3MM, M3.0	PCS	2
7	SCREW	5.4x11.9MM, M3.0	PCS	2
6	BRACKET	BRACKET FOR USB FEMALE	PC	1
5	PVC	MOLDING PVC(COLOR: BLACK)	G	12
4				
3	H. S. T.	HEAT SHRINK TUBEØ1.0x10MM (COLOR: BLACK)	PCS	2
2	USB	USB 4P FEMALE A TYPE CONTACTS(BRASS GOLD FLASH)	PCS	2
1	CABLE	(28AWGx1P+24AWGx2C) AEB, UL2725(COLOR: BLACK), #4.5±0.15MM	MM	330

UNLESS OTHERWISE SPECIFIED TOLERANCE :		ANGLES : 82°	
XX	±0.5	XX	±0.15
DO NOT SCALE DRAWING			
DRAWN BY		TITLE	
YU WEI		PRE-ASSEMBLED BLANKING PLATES C3110	
CHECKED BY	SIZE A	UNIT MM	PART NO. 294-9474
APPROVED BY	SCALE 4 : 5	THIRD ANGLE PROJECTION	REV. B
DWG NO.	ITEM NO.	DATE	PAGE 1 OF 1
	C5010UBAF2B040007D1E	07/11/2005	