



ENGLISH

Datasheet

**RS Pro Green, 50m Kynar Equipment Wire, 0.05 mm<sup>2</sup> CSA, 300 V**

RS Stock No: **209-4833**



## Product Details

RS Pro kynar equipment wire in green colour, is 50 m long with a cross sectional area of 0.05 mm<sup>2</sup> and an outer diameter of 0.5 mm. It has silver-plated copper solid conductor with kynar insulation.

## Features and Benefits

- Temperature range: -20 to +130°C
- Voltage rating of 150 Vrms
- Resists run back when soldering

**Specifications:**

Conductor Material	Silver Plated Copper
Insulation Material	Kynar
Sheath Colour	Green
Standards Met	RoHS Compliant
Length	50 m
Maximum Operating Temperature	+130°C
Minimum Operating Temperature	-20°C
Outer Diameter	0.5 mm
American Wire Gauge	30 AWG
Core Strands	1/0.25 mm
Cross Sectional Area	0.05 mm <sup>2</sup>
Current Rating	0.4 A
Number of Strands	1
Operating Temperature Range	-20 to +130°C
Size of Strands	0.25 mm
Type	Equipment Wire
Voltage Rating	300 V