


Spherical roller bearings, cylindrical and tapered bore



Principal dimensions			Basic load ratings		Fatigue load limit P_u	Speed ratings		Mass	Designation
d	D	B	dynamic	static		Reference speed	Limiting speed		
mm			kN		kN	r/min		kg	-
75	130	31	212	240	26,5	4800	6300	1,70	22215 E *



Calculation factors

- e 0,22
- Y_1 3
- Y_2 4,6
- Y_0 2,8