







12	OBSOLETE	56MM	1.050	21	1.230	44	116-147377-0
		44mm	.550	11	.730	24	115-147377-9
		88mm	2.450	49	2.630	100	115-147377-8
		88mm	1.950	39	2.130	80	115-147377-7
		72mm	1.450	29	1.630	60	115-147377-6
		56mm	1.200	24	1.380	50	115-147377-5
		56mm	.950	19	1.130	40	115-147377-4
		56mm	.700	14	.880	30	115-147377-3
		44mm	.450	9	.630	20	115-147377-2
		32mm	.200	4	-	10	115-147377-1
		56MM	1.050	21	1.230	44	4-147377-0-
		44mm	.550	11	.730	24	147377-9
		88mm	2.450	49	2.630	100	147377-8
		88mm	1.950	39	2.130	80	147377-7
		72mm	1.450	29	1.630	60	147377-6
		56mm	1.200	24	1.380	50	147377-5
		56mm	.950	19	1.130	40	147377-4
		56mm	.700	14	.880	30	147377-3
		44mm	.450	9	.630	20	147377-2
32mm	.200	4	-	10	147377-1		
TAPE WIDTHS		C	B	A	NO OF POSN	PART NUMBER	

THIS DRAWING IS A CONTROLLED DOCUMENT.		OWN: B. HAYMAKER 17JAN00		 Tyco Electronics Corporation Harrisburg, PA 17105-3608	
		CHK: J. MOSIER 17JAN00			
DIMENSIONS:		TOLERANCES, UNLESS OTHERWISE SPECIFIED:		NAME	
INCHES		APVD: J. MOSIER 17JAN00		HEADER ASSEMBLY, W/SIDE & END LATCHES, VERTICAL, SHROUDED, DOUBLE ROW, SURFACE MOUNT AMPMODU System 50, W/O HOLDDOWNS	
		PRODUCT SPEC		SIZE CAGE CODE DRAWING NO RESTRICTED TO A1 00779 C-147377 -	
		108-1093			
		APPLICATION SPEC			
		114-25035			
MATERIAL		FINISH		WEIGHT	
		SEE NOTES		CUSTOMER DRAWING	
				SCALE 4:1 SHEET 1 OF 1 REV E2	