



UNIX BASIC SIGNALING CABLE

Part Number: AP9823



Output	
Number of Ports	1
Physical	
Net Weight	0.45 KG
Maximum Height	229.00 mm
Maximum Width	102.00 mm
Maximum Depth	51.00 mm
Shipping Weight	0.45 KG
Shipping Height	229.00 mm
Shipping Width	102.00 mm
Shipping Depth	51.00 mm
Cord Length	2.00 meters

Connector A	DB9(Simple Signaling)
Connector B	DB9(Simple Signaling)
Mount Positions	Front
Environmental	
Operating Environment	0 - 45 °C
Operating Relative Humidity	0 - 95%
Operating Elevation	0-3000 meters
Storage Temperature	-15 - 45 °C
Storage Relative Humidity	0 - 95%
Storage Elevation	0-15000 meters
Conformance	
Standard Warranty	2 years repair or replace
Sustainable Offer Status	
RoHS	Compliant
REACH	REACH: Contains SVHCs
REACH SVHC	2.0 - DEHP - Bis(2-ethylhexyl) phthalate

/*
*