



ENGLISH

Datasheet

**RS Pro Round Fixed Height Feet, PD.2125BL 12.7mm,
PUR, +65°C -34°C**

RS Stock No: **248-524**



Product Details

RS Pro round anti-vibration feet in black colour, is made with PUR for long life durability. It has a diameter of 12.7 mm and overall height of 3.5 mm. It features excellent skid resistance with a high coefficient of friction and excellent resistance to moving and staining. It has a temperature rating of -34 to +65°C. This flexible polyurethane feet is suitable for indoor and limited outdoor applications.

Features and Benefits

- Long ageing resiliency and will not crack or harden
- Ideal for use on glass, aluminium, stainless steel, acrylic plastic, polyethylene, polystyrene, ABS, polypropylene and polycarbonate
- To ensure maximum adhesion, surfaces must be clean, dry and well unified
- Flexible polyurethane feet suitable for indoor and limited outdoor applications



ENGLISH

Specifications:

Foot Colour	Black
Foot Shape	Round
Material	PUR
Mounting Type	Adhesive
Type	Feet
Diameter	12.7 mm
Maximum Operating Temperature	+65°C
Minimum Operating Temperature	-34°C
Overall Height	3.5 mm
Finish	Gloss
Hardness	65 to 70 Shore A