



ENGLISH

Datasheet

## **RS Pro PVC Coated Galvanised Steel Flexible Conduit Black 20mm IP54 10m**

RS Stock No: **668-4786**



### **Product Details**

RS Pro cable conduit is 10 m long with a nominal diameter of 20 mm. It is made of galvanised steel with the addition of a thin, vacuum extruded PVC exterior coating, providing excellent weather protection without restricting the inner core flexibility. This IP40 rated conduit is perfect for high temperature continuous flexing applications requiring high mechanical protection. It is designed for commercial and industrial installations, including lighting, underfloor distribution, heating etc.

### **Features and Benefits**

- IP54 rated
- Temperature range of -20 to +80°C
- Comes in black colour
- Self extinguishing to UL94 V0



**Specifications:**

Coating Material	PVC
Colour	Black
Conduit Type	Flexible
IP Rating	IP54
Length	10 m
Material	Galvanised Steel
Maximum Operating Temperature	+80°C
Minimum Operating Temperature	-20°C
Nominal Diameter	20 mm
Operating Temperature Range	-20 to +80°C