

Datasheet

Stock No: 282-1253

RS Pro ELEG Aluminium Enclosure, IP65, 252 x 87 x 75



Product Details

IP65 With PCB Slots

- Sandblasted finish with 3mm wall thickness
- Neoprene gasket for IP65 protection
- Temperature range; -40°C to +100°C
- Four recessed screws secure lid into tapped holes
- Slots provided for mounting PCBs
- DIN rail can be fixed to the base

Note

DIN rail needs to be purchased separately and cut to required length.

Natural Finish Die Cast Aluminium Boxes



Specifications

Body Material	Die Cast Aluminium
External Dimensions	252 x 87 x 75
External Length	252 mm
External Width	87
External Height	75
IP Rating	IP65
Colour	Grey
Lid Colour	Grey
Series	ELEG
Weight	2.65kg
