

Datasheet

RS Pro Straight 75Ω Cable Mount BNC Connector Plug, Crimp Termination PSF 1/2

RS Stock No: **546-3709**



Product Details

RS Pro cable mount BNC connector plug has nickel plated body, gold plated centre contact and is suitable for PSF 1/2 cables. This 75 Ω straight BNC connector plug features bayonet coupling and crimp termination. It is suitable for a variety of applications including video signalling and test equipment.

Features and Benefits

- Nickel plated body
- Gold plated centre contact
- Crimp termination method

**Specifications:**

Body Orientation	Straight
Body Plating	Nickel
Cable Type	PSF 1/2
Contact Material	Brass
Contact Plating	Gold
Gender	Male
Impedance	75 Ω
Mounting Type	Cable Mount
Operating Frequency	1 GHz
Polarity	Normal
Termination Method	Crimp
Body Material	Brass
Insulation Material	PTFE
Operating Temperature Range	-20 to +80°C
Standards Met	RoHS Compliant
Voltage Rating	500 V (Working)