


# Housing - HC-D 15-AMLD - 1678363

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)

HEAVYCON panel mounting base D15, with single locking latch, height 26 mm



## Key commercial data

Packing unit	10 pc
GTIN	 4 017918 168537
Weight per Piece (excluding packing)	110.61 g
Custom tariff number	85389099
Country of origin	Germany

## Technical data

### Dimensions

Height	26 mm
Width	30.5 mm
Length	81 mm
Length of the assembly cutout	58 mm
Width of the assembly cutout	24 mm

### Ambient conditions

Degree of protection of housing (IP)	IP65 (When plugged in)
Ambient temperature (operation)	-40 °C ... 125 °C

### General

Note	For contact inserts HC-D15, A10
Type	D15
Housing type	Panel mounting base
Locking type	With single locking latch
Screw connection	none
Protective cover	Yes
Housing material	Aluminum die-cast

# Housing - HC-D 15-AMLD - 1678363

## Technical data

### General

Housing surface material	Powder-coated, gray
Material lock	Steel, galvanized
Material, protective cover	Polyamide

## Classifications

### eCl@ss

eCl@ss 4.0	27140816
eCl@ss 4.1	27140816
eCl@ss 5.0	27143424
eCl@ss 5.1	27143424
eCl@ss 6.0	27143424
eCl@ss 7.0	27440209
eCl@ss 8.0	27440209

### ETIM

ETIM 2.0	EC000437
ETIM 3.0	EC000437
ETIM 4.0	EC000437
ETIM 5.0	EC000437

### UNSPSC

UNSPSC 6.01	31261502
UNSPSC 7.0901	31261502
UNSPSC 11	31261502
UNSPSC 12.01	31261502
UNSPSC 13.2	31261502

## Approvals

### Approvals

---

Approvals

GOST

---

Ex Approvals

---

Approvals submitted

---

# Housing - HC-D 15-AMLD - 1678363

## Approvals

Approval details



## Drawings

Dimensioned drawing

Panel cutout

Dimensioned drawing

