

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [84507-0012](#)
Status: **Active**
Overview: XRC™ (Extra Rugged Circular) Sealed Plugs and Receptacles
Description: XRC™ Sealed Plug with Socket Insert, Shell Size 18, 14 Circuits, Blue Ring

Documents:

[Drawing \(PDF\)](#) [Application Specification AS-84501-001 \(PDF\)](#)
[Product Specification PS-84501-001 \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

UL E152602

General

Product Family Crimp Housings
 Series [84507](#)
 Application Power, Wire-to-Wire
 Comments IP67 rated; conforms to UL 1977. NOT suitable for automotive applications with requirements such as USCAR-2, USCAR-25, GMW3191, AK Testing, J2030, Volvo Technology Requirements, and Toyota Connector Spec (TCS)
 MolexKits Yes
 More Detailed Tech Information Extra thin wall wire seals
 Overview XRC™ (Extra Rugged Circular) Sealed Plugs and Receptacles
 Product Name XRC™
 UPC 822350758543

Physical

Circuits (maximum) 14
 Flammability 94V-0
 Gender Plug
 Glow-Wire Compliant No
 Keying to Mating Part Yes
 Lock to Mating Part Yes
 Net Weight 44.090/g
 Number of Rows 0
 Packaging Type Tray
 Panel Mount Yes
 Pitch - Mating Interface N/A
 Pitch - Termination Interface N/A
 Polarized to Mating Part Yes
 Ports 1
 Stackable No
 Temperature Range - Operating -55°C to +125°C

Material Info

Reference - Drawing Numbers

Application Specification AS-84501-001
 Product Specification PS-84501-001
 Sales Drawing SD-84507-002



EU RoHS

ELV and RoHS Compliant
REACH SVHC Contains SVHC: No
Low-Halogen Status Not Reviewed

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
 For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

[84507Series](#)

Mates With

[84502](#) Receptacle

Use With

[84525](#) XRC™ Sealed Terminal Socket