



TOLERANCES:  $\pm 0.30$  mm ( $\pm 0.012$  in)

宣又實

繪圖 DRA'D BY  
JACKY

日期 DATE  
2010/1/20

材質 MATE.  
ALUMINIUM ALLOY ADC-12

圖名 TITLE:  
HQ021

圖號 DWG NO:

版次 REVISID:  
A

ITEM NO	DESCRIPTION
HQ021	NATURAL ALUMINIUM BOX<WITOUT THE GASKET>
HQ021S	@@ IP67 RATING @@<WITH THE SILICON GASKET>
HQ021EMS	@@ IP67 RATING @@<WITH THE SILICON & SHIELDED GASKET>

**MATERIAL:** ALUMINUM ALLOY #ADC-12

**FINISH:** NATURAL (NO SUFFIX)  
 GRAY (SUFFIX -LG)  
 BLACK (SUFFIX -BK)

- 1) FOUR(4) M4 x 20mm (0.787") LG. SCREWS SUPPLIED FOR ASSEMBLY OF COVER TO BODY.
- 2) ALL HOLE DIAMETERS HAVE ±0.10mm TOLERANCE  
 ALL OTHER DIMENSIONS HAVE ±0.30 mm TOLERANCE



宣又實	繪圖	DRA'D BY	日期	DATE	材質	MATE.	圖名TITLE:	圖號DWG NO:	版次REVISID:
		JACKY		2010/1/20		ALUMINIUM ALLOY ADC-12	HQ021		A