

Datasheet

RS Pro Straight Cable Mount SMC Connector, Plug, Clamp Termination, RG174 A/U

RS Stock No: **546-3412**



Product Details

RS Pro cable mount SMC connector plug offers clamp termination. It includes soldered centre contact. This straight connector plug is compatible with RG174 A/U cable type.

Features and Benefits

- Gold-plated
- Suitable for use with RG174 cable
- Centre contact is soldered

**Specifications:**

Body Orientation	Straight
Body Plating	Gold
Cable Type	RG174 A/U
Contact Material	Brass
Contact Plating	Gold
Gender	Male
Impedance	50 Ω
Mounting Type	Cable Mount
Operating Frequency	10 GHz
Size	Subminiature
Termination Method	Clamp
Dimensions	18.6 x 6 mm
Operating Temperature Range	-65 to +165°C