

General Information

| | |
|------------------------|--|
| Extended Product Type: | 316RS6 |
| Product ID: | 2CMA193106R1000 |
| EAN: | 7392696931069 |
| Catalog Description: | Surface socket-outlet, 6h, 16A, IP44, 3P+E |
| Long Description: | Surface socket-outlet, earthing sleeve position 6h, rated current 16A, IP44 splashproof, 3-poles+earth, frequency 50-60 Hz, color code Red |

Categories

Products » Low Voltage Products and Systems » Industrial Plugs and Sockets » Plugs & Sockets » Surface Socket Outlets

Ordering

| | |
|-------------------------|---------------------|
| EAN: | 7392696931069 |
| Minimum Order Quantity: | 10 piece |
| Country of Origin: | Czech Republic (CZ) |

Dimensions

| | |
|---------------------|---------|
| Product Net Width: | 79 mm |
| Product Net Height: | 132 mm |
| Product Net Length: | 100 mm |
| Product Net Depth: | 132 mm |
| Product Net Weight: | 0.24 kg |

Container Information

| | |
|-------------------------------|---------------|
| Package Level 1 Width: | 143 mm |
| Package Level 1 Length: | 397 mm |
| Package Level 1 Height: | 187 mm |
| Package Level 1 Gross Weight: | 0.24 kg |
| Package Level 1 EAN: | 7392696931069 |
| Package Level 1 Units: | 10 piece |

Environmental

| | |
|--------------|--|
| RoHS Status: | Planned to follow EU Directive 2002/95/EC August 18, 2005 and amendment after 2006-03-01 |
|--------------|--|

Certificates and Declarations (Document Number)

| | |
|---------------------------------|-----------------|
| Declaration of Conformity - CE: | 2CMC700005D0001 |
| Environmental Information: | 2CMC700001D0002 |
| RoHS Information: | 2CMC700057D0001 |

Additional Information

| | |
|----------------------------------|---|
| Additional Information: | Cable entry, flexible membrane and metric threaded M20 insert for top cable entry.Rear knock-out cable entry. |
| Cable Cross-Section: | 1.5 ... 4 mm ² |
| Color: | Red |
| Degree of Protection: | acc. to IEC 60529 IP44 |
| Enclosure Material: | Thermoplastic |
| Frequency (f): | 50 Hz |
| Function: | Surface socket outlet |
| IIT Publishing Status: | Level 0 - Information enabled |
| Invoice Description: | Ind. P&S#316RS6 |
| Number of Poles: | 4 |
| Object Classification Code: | 2CMT005069 |
| Product Main Type: | RS |
| Product Name: | Industrial Socket Outlet |
| Protection Type: | Splashproof |
| Rated Current (I _n): | 16 A |
| Rated Voltage (U _r): | 380 ... 415 V |
| RoHS Date: | L23 |
| Standards: | IEC 60309-1,-2 |
| Suitable For: | Surface Socket Outlets |

Suitable for Product Class: Industrial Plugs and Sockets

Classifications

E-nummer: 2416449

UNSPSC: 39120000

