

# CR-P/M 52B



Products → Low Voltage Products and Systems → Control Products → Electronic Relays and Controls  
→ Interface Relays and Optocouplers

## General Information

<b>Extended Product Type:</b>	CR-P/M 52B
<b>Product ID:</b>	1SVR405653R0000
<b>EAN:</b>	4013614528750
<b>Catalog Description:</b>	CR-P/M 52B Pluggable module
<b>Long Description:</b>	The CR-P/M 52B plug-in module is a pluggable function module for the CR-P and CR-M range sockets. This module provides arc elimination. The rated control supply voltage is 6-24 V AC/DC.

## Additional Information

<b>Accessory Type:</b>	Pluggable Function Module
<b>CSA Certificate:</b>	CSA_262671-2785566
<b>Country of Origin:</b>	China (CN)
<b>Customs Tariff Number:</b>	85389099
<b>Data Sheet, Technical Information:</b>	2CDC117007D0204
<b>Declaration of Conformity - CE:</b>	1SVD982020-0001
<b>E-nummer:</b>	4005383
<b>EAC Certificate:</b>	EAC_RU_C-PL.ME77.B.01873
<b>EAN:</b>	4013614528750
<b>EPLAN Catalog Tree:</b>	Electrical engineering / Relays, contactors / General
<b>EPLAN Function Definition:</b>	Protective circuit / Protective circuit, 2 connection points / Protective circuit, RC network A1_A2
<b>ETIM 4:</b>	EC002586 - Accessories for switching relay
<b>ETIM 5:</b>	EC002586 - Accessories for switching relay
<b>ETIM 6:</b>	EC002586 - Accessories for switching relay
<b>Environmental Information:</b>	1SAA981009-2401
<b>Function:</b>	Accessory for interface relays CR-M Accessory for interface relays CR-P
<b>IIT Publishing Status:</b>	Level 0 - Information enabled
<b>Industrial IT Certification Level:</b>	0
<b>Instructions and Manuals:</b>	2CDC117007D0204
<b>Invoice Description:</b>	CR-P/M 52B Pluggable module
<b>Minimum Order Quantity:</b>	10 piece
<b>Object Classification Code:</b>	K
<b>Output:</b>	none
<b>Output Signal:</b>	none
<b>Package Level 1 EAN:</b>	4013614373862
<b>Package Level 1 Gross Weight:</b>	0.032 kg
<b>Package Level 1 Height:</b>	180 mm
<b>Package Level 1 Length:</b>	9 mm
<b>Package Level 1 Units:</b>	10 piece
<b>Package Level 1 Width:</b>	130 mm
<b>Power Loss:</b>	-
<b>Product Main Type:</b>	CR-P/M
<b>Product Name:</b>	Pluggable Function Module
<b>Product Net Depth:</b>	9 mm

<b>Product Net Height:</b>	24 mm
<b>Product Net Weight:</b>	0.003 kg
<b>Product Net Width:</b>	13 mm
<b>Rated Control Supply Voltage (U<sub>s</sub>):</b>	6 ... 24 V AC/DC 6 ... 24 V AC
<b>Regulatory Compliance Mark (RCM):</b>	No
<b>RoHS Date:</b>	1146
<b>RoHS Information:</b>	1SVD982020-0001
<b>RoHS Status:</b>	Following EU Directive 2011/65/EC
<b>Selling Unit of Measure:</b>	piece
<b>Short Description:</b>	CR-P/M 52B Pluggable module
<b>Standards:</b>	EN 50581 IEC/EN 61984 UL 508 CAN/CSA C22.2 No. 14
<b>Sub-Function:</b>	Pluggable function module for pcb and miniature relay sockets
<b>Sub-Function 2:</b>	Spark quenching
<b>Suitable For:</b>	CR-P CR-M
<b>UNSPSC:</b>	43172000
<b>cURus Certificate:</b>	cURus508_E244328
<b>eClass:</b>	7.0 27379208

