

Accessories for Wireless products

// Field strength indicator EPM 300 Order no.: 90598005

Features/Options

- Mobile field strength indicator EPM 300 for link range testing
- To measure and indicate the electrical field strength
- Battery not included, requires AA/LR06 cell
- Order unit: 1 piece

EPM 300



Technical Data

Standards	R&TTE: EN 300 220 (868 Mhz); FCC: CFR-47 Part 15 (315 Mhz); RoHS
Degree of protection	IP 54 per IEC/EN 60529
Protocol	EnOcean
Ambient temperature	0 °C ... + 45 °C
Storage and shipping temperature	-15 °C ... +65 °C
Voltage supply	AA/LR06 cell (recommended Energizer L91)
Frequency	868,3 MHz
Sensing range	max. 300 m outside, max. 30 m inside
Dimensions	110 x 70 x 25 mm
Weight	85 g (w/o battery)
Weight	80g

Errors and omissions excepted.