

Datasheet

## RS Pro SPDT Roller Lever Microswitch, 7 A @ 250 V ac

RS Stock No: **468-3851**



### Product Details

RS Pro SPDT microswitch is suitable for operating temperatures ranging from -62 to +80°C. This roller lever switch withstands currents up to 7 A at 250 V ac. It has aluminium case for added durability.

### Features and Benefits

- Environmentally sealed in epoxy and enclosed in a corrosion-resistant aluminium housing
- Stainless steel pin plunger with silicone rubber seal
- Protected against atmospheric pressure variations, moisture, vapour and a wide range of contaminants
- May be used in areas specified in zone 2 of BS5501
- Supplied with stainless steel lever actuator and fittings
- Complete with 300 mm PTFE covered leads
- Operating temperature of -62 to +80°C

**Specifications:**

Actuator Type	Roller Lever
Case Material	Aluminium
Contact Configuration	SPDT
Contact Current Rating	7 A at 250 V ac
Contact Material	Silver
Hazardous Area Certification	ATEX
Maximum Operating Temperature	+80°C
Mechanical Life	1000000 operations
Minimum Operating Temperature	-62°C
Operating Force	3.34 N
Operating Temperature Range	-62 to +80°C
Terminal Type	Pre-Wired