

Datasheet

RS Pro Straight 50Ω Cable Mount SMA Connector, jack, Crimp Termination

RS Stock No: **546-3355**



Product Details

RS Pro straight 50Ω cable mount SMA connector is suitable for use with RG174A/ U cable. It features reliable and quick connect/disconnect system. This female connector operates at a voltage rating of 500 V dc or ac and temperature of -55 to +155°C.

Features and Benefits

- Reliable and quick connect/disconnect system
- Recommended for use with RG174A/ U cable
- Voltage rating of 500 V dc or ac and temperature of -55 to +155°C
- Crimp termination method

**Specifications:**

Body Orientation	Straight
Gender	Female
Impedance	50 Ω
Mounting Type	Cable Mount
Polarity	Normal
Size	Subminiature
Termination Method	Crimp
Voltage Rating	500 V ac/dc
Body Material	Brass
Operating Temperature	-40 to +80°C
Type	SMB
VSWR (Voltage Standing Wave Ratio)	1.3 at 1 GHz